



TECHNICAL DATA

Cu Earthing Strap

Temperature range	-20°C to +125°C
individual strand size	0.2 mm

■ STRUCTURE

- Material: copper tinned

■ PROPERTIES

- rounded contacts
- contact areas made of seamless, pressed ferrules

■ APPLICATION

- automobile industry
- robots
- Control cabinet construction
- for EMC applications (interference elimination)

■ NOTES

- other lengths and inner diameters available on request
- Legend:
Dimensions
B1 - Stud hole
B2 - Stud hole
L - Length

Part no.	Type	Cross-sec. mm ²	Length mm	Boring mm	Packaging unit (in pc.)
11008412	HELU-MB-CUv-6-150-4,5/6,5-R	6	150.0	4.5 / 6.5	50
11018291	HELU-MB-CUv-6-150-6,5/6,5-R	6	150.0	6.5 / 6.5	50
11008415	HELU-MB-CUv-6-300-6,5/6,5R	6	300.0	6.5 / 6.5	50
11008411	HELU-MB-CUv-6-500-6,5/6,5-R	6	500.0	6.5 / 6.5	50
11008413	HELU-MB-CUv-6-200-8,5/8,5-R	6	200.0	8.5 / 8.5	50
11008421	HELU-MB-CUv-10-200-6,5/6,5-R	10	200.0	6.5 / 6.5	50
11017752	HELU-MB-CUv-10-200-6,5/8,5-R	10	200.0	6.5 / 8.5	50
11008423	HELU-MB-CUv-10-300-6,5/6,5-R	10	300.0	6.5 / 6.5	50
11017753	HELU-MB-CUv-10-300-6,5/8,5-R	10	300.0	6.5 / 8.5	50
11008422	HELU-MB-CUv-10-200-8,5/8,5-R	10	200.0	8.5 / 8.5	50
11008424	HELU-MB-CUv-10-300-8,5/8,5-R	10	300.0	8.5 / 8.5	50
11008425	HELU-MB-CUv-10-400-8,5/8,5-R	10	400.0	8.5 / 8.5	50
11017610	HELU-MB-CUv-10-500-8,5/8,5-R	10	500.0	8.5 / 8.5	50
11021421	HELU-MB-CUv-16-150-6,5/6,5-R	16	150.0	6.5 / 6.5	50
11008443	HELU-MB-CUv-16-200-6,5/6,5-R	16	200.0	6.5 / 6.5	50
11008445	HELU-MB-CUv-16-200-6,5/8,5-R	16	200.0	6.5 / 8.5	50

HELU-MB-CUv



Part no.	Type	Cross-sec. mm ²	Length mm	Boring mm	Packaging unit (in pc.)
11008446	HELU-MB-CUv-16-250-6.5/8.5-R	16	250.0	6.5 / 8.5	50
11008444	HELU-MB-CUv-16-300-6.5/6.5-R	16	300.0	6.5 / 6.5	50
11008447	HELU-MB-CUv-16-300-6.5/8.5-R	16	300.0	6.5 / 8.5	50
11008442	HELU-MB-CUv-16-100-8.5/8.5-R	16	100.0	8.5 / 8.5	50
11008450	HELU-MB-CUv-16-1200-8.5/8.5-R	16	1200.0	8.5 / 8.5	50
11017281	HELU-MB-CUv-16-150-8.5/8.5-R	16	150.0	8.5 / 8.5	50
11008378	HELU-MB-CUv-16-200-8.5/8.5-R	16	200.0	8.5 / 8.5	50
11017273	HELU-MB-CUv-16-300-8.5/10.5-R	16	300.0	8.5 / 10.5	50
11008379	HELU-MB-CUv-16-300-8.5/8.5-R	16	300.0	8.5 / 8.5	50
11017756	HELU-MB-CUv-16-400-8.5/6.5-R	16	400.0	8.5 / 6.5	50
11008441	HELU-MB-CUv-16-400-8.5/8.5-R	16	400.0	8.5 / 8.5	50
11017286	HELU-MB-CUv-16-450-8.5/10.5-R	16	450.0	8.5 / 10.5	50
11008448	HELU-MB-CUv-16-500-8.5/8.5-R	16	500.0	8.5 / 8.5	50
11008449	HELU-MB-CUv-16-600-8.5/8.5-R	16	600.0	8.5 / 8.5	50
11008461	HELU-MB-CUv-25-200-8.5/8.5-R	25	200.0	8.5 / 8.5	50
11008462	HELU-MB-CUv-25-300-8.5/8.5-R	25	300.0	8.5 / 8.5	50
11017762	HELU-MB-CUv-25-500-8.5/8.5-R	25	500.0	8.5 / 8.5	50
11009170	HELU-MB-CUv-35-500-8.5/8.5-R	35	500.0	8.5 / 8.5	50
11009219	HELU-MB-CUv-50-300-10.5/10.5-R	50	300.0	10.5 / 10.5	50