

# UNI-DICHT-VK-PC



## TECHNICAL DATA

PC gland body

Temperature range -20°C to +100°C

## STRUCTURE

- Material: Polycarbonat (PC)

## PROPERTIES

- halogen-free
- phosphor-free
- silicone-free
- cadmium-free
- easy to assemble, time and cost savings

## APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- for fitting with TPE sealing inserts

## NOTES

- The gland body M20x1.5 part no. 11019751 is suitable for PG 11 inserts; part no. 11019752 is suitable for PG 13.5 inserts.
- Legend:  
Dimensions  
TD - Thread Diameter  
TL - Thread Length  
SZ - Spanner Size

### metric thread

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)	Colour
11019749	M12 x 1.5	8.0	15	50	grey (RAL 7035)
11019750	M16 x 1.5	9.0	19	50	grey (RAL 7035)
11019751	M20 x 1.5	9.0	24	50	grey (RAL 7035)
11019752	M20 x 1.5	9.0	24	50	grey (RAL 7035)
11019753	M25 x 1.5	9.0	30	50	grey (RAL 7035)
11019754	M32 x 1.5	11.0	36	25	grey (RAL 7035)
11019755	M40 x 1.5	11.5	46	10	grey (RAL 7035)
11019756	M50 x 1.5	14.0	56	5	grey (RAL 7035)

### PG thread

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)	Colour
11019757	PG 9	9.0	19	50	grey (RAL 7035)
11019758	PG 11	9.0	22	50	grey (RAL 7035)
11019759	PG 13.5	9.0	24	50	grey (RAL 7035)
11019760	PG 16	9.0	27	50	grey (RAL 7035)
11019761	PG 21	11.0	33	25	grey (RAL 7035)
11019762	PG 29	11.0	43	10	grey (RAL 7035)
11019763	PG 36	14.0	53	5	grey (RAL 7035)