

# UNI-DICHT-ASI-PC



## TECHNICAL DATA

PC gland body

Temperature range -20°C to +100°C

### ■ STRUCTURE

- Material: Polycarbonat (PC)
- Seal: thermoplastic vulcanizates (TPV)

### ■ PROPERTIES

- optimum strain relief through rubber seal
- easy to assemble, time and cost savings
- Large-area sealing

### ■ NOTES

- Legend:  
Dimensions  
TD - Thread Diameter  
TL - Thread Length  
SZ - Spanner Size

## metric thread

Size	Sealing insert colour	Thread length mm	Spanner size mm	Packaging unit (in pc.)	grey (RAL 7035) Part no.
M20 x 1.5	grey, left	9.0	24	50	<b>11019764</b>
M20 x 1.5	grey, right	9.0	24	50	<b>11019765</b>