

TY-RAP®-D



TECHNICAL DATA

Detectable Cable Ties

Temperature range -40°C to +85°C

■ PROPERTIES

- halogen-free

■ STRUCTURE

- Material: siehe Tabelle
- Flammability acc. to UL 94 (HB)

Polyamid (PA) - 6.6

Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	blue Part no.
TY523MR-NDT	93.0	2.3	16	50	100	11020463
TY524MR-NDT	140.0	3.6	35	160	100	11020464
TY525MR-NDT	186.0	4.6	45	200	100	11020465
TY528MR-NDT	361.0	4.8	102	220	100	11020466
TY528MR-NDT	345.0	6.9	102	540	50	11020467

Polypropylen (PP)

Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	blue Part no.
TY523MR-PDT	93.0	2.3	16	50	100	908529
TY525MR-PDT	186.0	4.6	45	135	100	908530
TY528MR-PDT	361.0	4.8	102	135	100	908531
TY527MR-PDT	345.0	6.9	95	267	50	908532