

HELUcond W-CO-PA-12-MOD-BS-V2



Corrugated tubes made of PA12, dividable



TECHNICAL DATA

PA Corrugated tubes

Temperature range -50°C to +110°C

■ STRUCTURE

- Material: Polyamide (PA) 12, MOD BS V2
- Flammability acc. to UL 94 : V2

■ PROPERTIES

- halogen-free
- cadmium-free
- resistant to: weather-resistant
- highly resistant to alternate bending strength

Colour: black

Part no.	Type	trade size mm	Inner Ø mm	Outer Ø mm, approx.	Bending radius mm	Packaging unit (in m)
11020606	2PDSM-07B.50	7.0	6.3	10.0	20.0	50
11020607	2PDSM-10B.50	10.0	8.8	13.5	25.0	50
11020608	2PDSM-11B.50	11.0	11.0	16.1	25.0	50
11020609	2PDSM-14B.50	14.0	13.2	18.7	30.0	50
11020610	2PDSM-16B.50	16.0	16.0	21.5	35.0	50
11020611	2PDSM-20B.50	20.0	20.2	25.7	45.0	50
11020612	2PDSM-23B.50	23.0	23.9	31.3	55.0	50
11020613	2PDSM-29B.25	29.0	27.3	35.5	105.0	25
11020614	2PDSM-37B.25	37.0	32.5	43.2	130.0	25
11020615	2PDSM-45B.25	45.0	43.1	54.2	135.0	25
11020616	2PDSM-70B.10	70.0	67.0	79.8	175.0	10
11020617	2PDSM-100B.10	100.0	87.5	102.5	195.0	10