

Airflex-K



TECHNICAL DATA

Protection tube

Temperature range	-25°C to +70°C short term up to +100°C
Protection class	IP 68

■ STRUCTURE

- Material: Polyvinyl chloride (PVC) with hard plastic helix
- Flammability acc. to V0 acc. to UL 94

■ PROPERTIES

- silicone-free
- cadmium-free

■ APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction
- Type K cable protection tube with integrated hard plastic winding.

■ NOTES

- Suitable connection glands: USK, LK-I, MTG-US und MTG-LI

Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey Part no.
10.0	14.0	50	11024498
13.0	17.0	50	11024499
15.0	19.0	50	11024500
16.0	21.0	50	11024501
21.0	27.0	50	11024502
29.0	36.0	25	11024503
38.0	45.0	25	11024504
48.0	56.0	25	11024505