

HELUTOP HT RJ45

for RJ45 pre-assembled cables



TECHNICAL DATA

PA cable gland

Temperature range -20°C to +80°C
Protection class IP 68 - 5 bar, 30 min.

STRUCTURE

- Material: Polyamide (PA) 6
- Seal: Chloroprene rubber (CR)
- Flammability acc. to UL 94 (V2)

TESTS

- Test standard EN 60423

APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction

NOTES

- separable seal
- Legend:
Dimensions
H - Height
TL - Thread Length
SZ - Spanner Size

metric thread

| Size | Cable Ø from / to mm | Height mm | Thread length mm | Spanner size mm | Packaging unit (in pc.) | grey | grey | black |
|-----------|-------------------------|-----------|---------------------|--------------------|----------------------------|------------------------|------------------------|------------------------|
| | | | | | | (RAL 7035) Part no. | (RAL 7001) Part no. | (RAL 9005) Part no. |
| M20 x 1.5 | 3.0 - 6.0 | 31.9 | 10.0 | 27 | 50 | 11024765 | 11024766 | 11024767 |
| M25 x 1.5 | 3.0 - 6.0 | 38.4 | 10.0 | 33 | 25 | 11025434 | 11025435 | 11025436 |