

# CV Compact 45°



## TECHNICAL DATA

### Elbow brass nickel-plated conduit gland

Temperature range	-45°C to +105°C
Protection class	IP 67

## ■ STRUCTURE

- Material: Brass nickel plated
- Grounding sleeve: steel
- Sealing ring: Polyamide (PA)

## ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction

## ■ NOTES

- Suitable for metallic protection tubes: Anaconda Sealtite®: EF, HTDL, OR, HC, HCX, ZHLS, HFX

### metric thread

Part no.	Size	Suitable for tube ND	Suitable for tube outer Ø mm	Spanner size mm	Thread length mm	Packaging unit (in pc.)
11025414	M16 x 1.5	3/8	12.6	26	10.0	10
11025415	M20 x 1.5	3/8	12.6	26	10.0	10
11025416	M20 x 1.5	1/2	16.1	26	10.0	10
11025417	M25 x 1.5	3/4	21.1	35	10.0	5
11025418	M32 x 1.5	1	26.8	45	12.0	5
11025419	M40 x 1.5	1 1/4	35.4	53	13.0	2
11025420	M50 x 1.5	1 1/2	40.3	62	14.0	2
11025421	M63 x 1.5	2	51.6	76	16.0	2