



Technical data

- Special Neoprene-flat cable adapted to DIN VDE 0250 part 809
- **Temperature range**
flexing -30°C to +80°C
fixed installation -40°C to +80°C
- **Nominal voltage** U₀/U 300/500 V
- **Test voltage** 3000 V
- **Minimum bending radius**
10x cable thickness
- **Radiation resistance**
up to 50x10⁵ cJ/kg (up to 50 Mrad)

Cable structure

- Copper-conductor bare or tinned to DIN VDE 0295, BS 6360, IEC 60228
- Conductor construction
35-120 mm² class 5: fine-wire
1,5-25 mm² class 6 col.4: extra-fine-wire
- Special rubber core insulation
- Core identification to DIN VDE 0293
- up to 5 cores coloured
- from 7 cores, black with continuous white numbering
- Cores laying parallel
- GN-YE conductor
- Outer sheath of special rubber 5GM3, to DIN VDE 0207 part 21
- Sheath colour black

Properties

- Special rubber outer sheath, cold-resistant
- Extensively oil resistant, oil-/chemical resistance see table Technical Informations
- Extremely small bending radius
- High flexibility
- Minimum waste of space
- Packaging possibility
- Outdoor application

Tests

- Behaviour in fire to DIN VDE 0482-332-1-2
DIN EN 60332-2-1, IEC 60332-1 (equivalent DIN VDE 0472 part 804 test method B)

Note

- G = with green-yellow conductor
- Part no. 28007 and 28013 (6x4).
- AWG sizes are approximate equivalent values. The actual cross-section is in mm².

Application

Neoprene type of flat cables are used mainly as trailing cable for crane installations, floor conveyer systems and shelf control units. These cables are also available for export with UL-approval on request.

Installation notes

Cables reels with flat cables must be transported in standing position on the flange. A bending flexibility can be achieved on a plane surface. For this purpose, the corresponding fitting instructions should be followed.

- Put the cable trolly on the guiding rail or upon carrier beam and push them together at the starting point. The distance between the bedding surface of two cable trollys must be wider than the double thickness of a cable-packet.
- During the packaging performance, it must be started with the smaller cross-section which lays on the bedding surface and will be builded successively so that the biggest cross-section is laying on the top.
- Further, be careful of a symmetrical load distribution.
- In case of multicore flat cables with small cross-section, smaller than 2,5 mm², is very critical due to its low tensile stress. In such case, you should add 10% reserve wire for calculation.

CE = The product is conformed with the EC Low-Voltage Directive 2006/95/EC.

Part no.	No. cores x cross-sec. mm ²	Outer dimension app. mm	Cop. weight kg / km	Weight app. kg / km	AWG-No.	Part no.	No. cores x cross-sec. mm ²	Outer dimension app. mm	Cop. weight kg / km	Weight app. kg / km	AWG-No.
28001	4 G 1,5	5,9 x 16,2	58,0	234,0	16	28022	4 G 16	11,6 x 35,6	614,0	1430,0	6
28002	5 G 1,5	5,9 x 23,7	72,0	304,0	16	28023	5 G 16	12,2 x 48,2	768,0	1590,0	6
28003	7 G 1,5	5,9 x 30,5	101,0	391,0	16	28024	4 G 25	14,1 x 45,8	960,0	1890,0	4
28004	8 G 1,5	5,9 x 34,0	115,0	441,0	16	28025	5 G 25	14,7 x 58,3	1200,0	2215,0	4
28005	10 G 1,5	5,9 x 43,5	144,0	460,0	16	28026	7 G 25	15,3 x 78,7	1680,0	3000,0	4
28006	12 G 1,5	6,5 x 50,4	173,0	646,0	16	28027	4 G 35	15,8 x 50,8	1344,0	2460,0	2
28007	24 G 1,5 (6 x 4)	13,0 x 56,0	346,0	1290,0	16	28028	5 G 35	16,4 x 64,4	1680,0	2880,0	2
28008	4 G 2,5	7,2 x 19,6	96,0	316,0	14	28029	7 G 35	16,4 x 86,4	2352,0	4100,0	2
28009	5 G 2,5	7,2 x 27,8	120,0	391,0	14	28030	4 G 50	18,6 x 60,2	1920,0	3385,0	1
28010	7 G 2,5	7,2 x 36,1	168,0	533,0	14	28031	4 G 70	21,0 x 68,0	2688,0	4480,0	2/0
28011	8 G 2,5	7,2 x 40,2	192,0	602,0	14	28032	4 G 95	24,1 x 78,6	3648,0	5990,0	3/0
28012	12 G 2,5	7,8 x 59,4	288,0	890,0	14	28033	4 G 120	25,5 x 84,2	4608,0	7240,0	4/0
28013	24 G 2,5 (6 x 4)	15,5 x 66,8	576,0	1480,0	14						
28014	4 G 4	8,8 x 24,2	154,0	506,0	12						
28015	5 G 4	8,8 x 33,4	192,0	621,0	12						
28016	7 G 4	8,8 x 42,5	269,0	851,0	12						
28017	4 G 6	9,6 x 27,4	230,0	661,0	10						
28018	5 G 6	9,6 x 37,4	288,0	740,0	10						
28019	7 G 6	9,6 x 47,2	403,0	1004,0	10						
28020	4 G 10	10,4 x 30,8	384,0	1027,0	8						
28021	5 G 10	10,4 x 41,6	480,0	1171,0	8						

Dimensions and specifications may be changed without prior notice. (RJ01)