

J-2Y(St)Y St III Bd 16 Mbits/s (Kat. 3) ISDN/EDV (Z = 100 Ohm), meter marking



Technical data

- Special core insulation of PE adapted to DIN VDE 0815 and 0816
- **Conductor loop-resistance**
max. 130 Ohm/km
- **Temperature range**
flexing -5°C to +70°C
fixed installation -40°C to +70°C
- **Operating peak voltage** 300 V
(not for heavy current installation purposes)
- **Test voltage** 800 V
- **Insulation resistance**
min. 5 GOhm x km
- **Mutual capacitance** 48 nF/km
- **Characteristic impedance (Z)**
at 4-16 MHz: 100 Ohm 15%
- **Capacitance unbalance**
K₁ max. 400 pF/300 m
K₉-K₁₂ max. 100 pF/300 m
- **Rel. velocity ratio**
approx. 0,66
- **Attenuation** at
1 MHz: 28 dB/km
4 MHz: 47 dB/km
5 MHz: 51 dB/km
10 MHz: 65 dB/km
15 MHz: 76 dB/km
16 MHz: 78 dB/km
20 MHz: 89 dB/km
- **Cross-talk attenuation**
from 4 MHz up to 16 MHz
for 2 pairs: min. 40 dB
4 pairs and above: min. 25 dB
- **Minimum bending radius**
stationary 10x cable Ø

Cable structure

- Bare copper-conductor, single-wire
- Core insulation of PE
- Colour coding to DIN VDE 0815
- Conductors twisted to quads
- 5 quads twisted to units
- Static screen of plastics coated alu foil with drain wire 0,6 mm Ø
- Outer sheath of PVC, flame retardant, compound type YM1 to DIN VDE 0207 part 5
- Sheath colour grey (RAL 7032)
- with meter marking

Properties

- PVC outer sheath: self-extinguishing and flame retardant to DIN VDE 0482-332-1-2, DIN EN 60332-1-2/IEC 60332-1 (equivalent DIN VDE 0472 part 804 test method B)
- The materials used in manufacture are cadmium-free and contain no silicone and free from substances harmful to the wetting properties of lacquers

Application

Used as data transmission and connection cable suitable for fixed installation in and under plaster, for data transmission applications, for periphery instrument data processing computers. Suitable for transmission of analog- and digital signals up to 16 Mbit/s. High cross-talk attenuation values. Suitable as connecting cable for periphery equipment, data processing systems, monitors, printers and cash register systems. The static screen (St) screen assures a disturbance-free data and signal transmission for measuring and control systems. These cables are not allowed for purposes of high current and power installation.

CE= The product is conformed with the EC Low-Voltage Directive 2006/95/EC.

Part no.	No. pairs x cross-sec. mm	Outer Ø approx. mm	Cop. weight kg / km	Weight approx. kg / km	
33200	2 x 2 x 0,6	6,1	13,0	44,0	-
33201	4 x 2 x 0,6	7,5	24,0	80,0	-
33202	6 x 2 x 0,6	7,6	35,0	86,0	-
33203	8 x 2 x 0,6	8,8	46,0	105,0	-
33204	10 x 2 x 0,6	8,8	58,0	112,0	-
33205	20 x 2 x 0,6	12,9	116,0	218,0	-

Part no.	No. pairs x cross-sec. mm	Outer Ø approx. mm	Cop. weight kg / km	Weight approx. kg / km	
33206	30 x 2 x 0,6	14,0	172,0	302,0	-
33207	40 x 2 x 0,6	15,5	229,0	376,0	-
33208	50 x 2 x 0,6	17,3	266,0	480,0	-
33209	60 x 2 x 0,6	18,1	342,0	560,0	-
33210	80 x 2 x 0,6	22,0	455,0	748,0	-
33211	100 x 2 x 0,6	25,2	588,0	940,0	-

Dimensions and specifications may be changed without prior notice. (RB01)