



## Type

### Configuration

Housing material:	Steel plate, solid
Colour:	Grey similar to RAL 7035
Board:	3x8 mother board, number-coded
Push-on connector type:	RJ45(8/8)
Number of bushings:	24
Type of screen:	Overall screen
Screen removal:	metalized cable straps
Strain relief:	by means of cable straps
Cover lock:	Quick-action snap cover

### Patch panel category 24P 6EA 500MHz

### Connecting system

Connection type:	LSA plus - insulation piercing connections
Suitable for cable diameter:	0.4 - 0.64mm (AWG 26 - 22)
Insulation diameter, min.:	0,7 - 1,6 mm (PE)

### Assignment type

EIA/TIA 568 A + EIA/TIA 568 B

### Dimension

Width:	483 mm
Depth:	125 mm
Number of height modules (HM):	1
Fastening dimensions:	19"

### Norms and standards

HELUKAT® CONNECTING SYSTEMS® system component up to 500 MHz (10 GBit Ethernet) in accordance with category 6a EIA/TIA 568-B.2-10, IEEE 802.3an TM-2006, ISO/IEC 11801 (Amendment 1 JTC 1/SC N1255), ISO/IEC TR-24750 and EN 55022 (EMV).

### Application

As floor distributor in applications of digital and analog image, data and voice transmission.

### Part no.

**802024**

Dimensions and specifications may be changed without prior notice.

### Packing unit

**1**