



Type

Cable

Designation:
Sheath material:
Frequency:

Patch cable S/FTP halogenfree, Cat.6a 500 MHz (10GBit)

S/FTP 4x2xAWG 26/7 LSZH
LSZH
up to 500 MHz

Plug

Push-on connector type 1:
Push-on connector type 2:
Pin assignment:

RJ45 8(8)
RJ45 8(8)
1:1 acc. to TIA/EIA 568 B

Flame proof

acc. to IEC 60332-1-2

Norms and standards

HELUKAT® CONNECTING SYSTEMS® system components up to 500 MHz (10GBit) of category 6a / Class E in accordance with ISO 11801, 2nd edition, EN 50173, 2nd edition, and EIA/TIA 568 C-2.

Preferred types

Part no.	Sheath colour	Length in metres	Unit
802380	grey	1,0	10
802381	grey	2,0	10
802382	grey	3,0	10
802383	grey	5,0	10
802384	grey	7,5	10
802385	grey	10,0	10
804287	grey	15,0	10

Dimensions and specifications may be changed without prior notice.

Options

Naturally, we also offer other lengths and colors on request.