



Type

USB 2.0 A patch cable, industrial USB – drag chain application.

Cable

Designation:

USB 2.0 shielded cable PUR, up to 5,0m

Sheath material:

PUR

Frequency:

up to 400 MHz

Plug

Push-on connection 1:

USB A

Push-on connection 2:

USB A

Flame proof

Acc. to IEC 60332-1-2

Norms and standards

HELUKABEL® CONNECTING SYSTEMS® system components to 400 MHz in compliance with USB 2.0 Standard. Suitable for applications such as image processing (e.g. surveillance cameras), metrology and control technology.

Preferred types

Part no.	Sheath colour	Length in metres	Unit
802464	violet	0,5	10
802465	violet	1,0	10
802466	violet	2,0	10
802467	violet	3,0	10
802468	violet	5,0	10

Dimensions and specifications may be changed without prior notice.

Characteristics

- Suitable for use as a patch cable in harsh environments
- Suitable for drag chain and other constantly moving applications
- Application temperature from -20°C to +60°C
- High-speed data transmission rate to max. 480 Mbit/s
- 5.0m maximum transmission distance to terminal device.
- Suitable for light duty applications.

Options

Naturally, we also offer other lengths and connector types for IP applications on request.