

# Patch-Panels RJ45 unscreened



Category 6 / Class E



## Type

### Configuration

Housing material:	Steel plate, solid
Colour:	Black similar to RAL 9005
Board:	3x8 mother board, colour and number-coded
Push-on connector type:	RJ45(8/8)
Number of bushes:	24
Type of screen:	no
Strain relief:	by means of cable straps

### Connecting system

Connection type:	LSA plus - insulation piercing connections
Suitable for cable diameter:	0.4 - 0.64mm (AWG 26 - 22)
Insulation diameter, min.:	0,7 - 1,7 mm (PE)

### Assignment type

EIA/TIA 568 A + EIA/TIA 568 B

### Dimension

Width:	440 mm
Depth:	110 mm
Number of height modules (HM):	1
Fastening dimensions:	19"

### Norms and standards

HELUKAT® CONNECTING SYSTEMS® unscreened system component up to 250 MHz of category 6 / Class E in accordance with ISO 11801, EN 50173.

### Application

As floor distributor in applications of digital and analog image, data and voice transmission.

### Part no.

**802908**

Dimensions and specifications may be changed without prior notice.

### Packing unit

**1**