



Type

Configuration

Housing material:

Colour:

Board:

Push-on connector type:

Number of bushes:

Type of screen:

Screen removal:

Strain relief:

Cover lock:

Patch panel cat. 5e / class D 24P

Steel plate, solid

Grey similar to RAL 7035

3x8 mother board, colour and number-coded

RJ45(8/8)

24

Overall screen

via continuous screening tape

via pre-installed cable clips

Quick-action twist lock

Connecting system

Connection type:

Suitable for cable diameter:

Insulation diameter, min.:

LSA plus - insulation piercing connections

0.4 - 0.64mm (AWG 26 - 22)

0,7 - 1,7 mm (PE)

Assignment type

EIA/TIA 568 A + EIA/TIA 568 B

Dimension

Width:

483 mm

Depth:

148 mm

Number of height modules (HM):

1

Fastening dimensions:

19"

Norms and standards

HELUKAT® CONNECTING SYSTEMS® system component up to 100 MHz in category 5(e) / Class D in accordance with ISO 11801, 2nd edition, EN 50173, 2nd edition, EIA/TIA 568 B, and EN 55022 (EMC)

Application

As floor distributor in applications of digital and analog image, data and voice transmission.

Part no.

82010

Dimensions and specifications may be changed without prior notice.

Packing unit

1