



Type

RJ-45 UP socket class E 2P horizontal

Configuration

| | |
|-------------------------|--------------------------------|
| Housing material: | Die-cast, shielded |
| Colour: | Pure White similar to RAL 9010 |
| Board: | 1x2 |
| Push-on connector type: | RJ45(8/8) |
| Outlet direction: | 45 degrees |
| Number of bushes: | 2 |
| Type of screen: | Overall screen |
| Strain relief: | via pre-installed cable clips |
| Cable inlet: | horizontal |

Connecting system

| | |
|------------------------------|--|
| Connection type: | LSA plus - insulation piercing connections |
| Suitable for cable diameter: | 0,4 - 0,64mm (AWG 26 - 22) |
| Insulation diameter, min.: | 0,7 - 1,6 mm (PE) |

Assignment type

EIA/TIA 568 A + EIA/TIA 568 B

Dimension

| | |
|------------------------------|----------------|
| Dimensions of central plate: | 50 x 50mm |
| Installation dimensions: | 51 x 51 x 29mm |

Norms and standards

HELUKAT® CONNECTING SYSTEMS® system component up to 250 MHz in the permanent link of category 6 / Class E in accordance with ISO 11801, 2nd edition, EN 50173, 2nd edition, EIA/TIA 568 B, and EN 55022 (EMC)

Application

As workstation interface in applications of digital and analog image, data and voice transmission. Available as in-wall version (channel) and top-mount version (wall).

Part no.

82847

Dimensions and specifications may be changed without prior notice.

Packing unit

10