



TECHNICAL DATA

PA Corrugated tubes

Temperature range -40°C to +120°C
short term up to +150°C

■ STRUCTURE

- Material: Polyamide (PA) 6
- Flammability acc. to UL 94 (V2)

■ PROPERTIES

- halogen-free
- resistant to: fuels, mineral oils, greases
- Trouble-free retrofitting
- high mechanical strength

- simple installation of pre-fabricated lines

■ APPLICATION

- Machine and plant construction
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- The dividable and reclosable cable protection tube for subsequent mechanical protection of the cables. Repair of existing systems.

■ NOTES

- Suitable connection glands: COV

trade size mm	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	black Part no.
10.0	8.8	13.5	50	90061
14.0	13.2	18.7	50	90062
20.0	20.2	25.7	50	90063
23.0	23.9	31.3	50	90064
37.0	32.5	43.2	25	90065
45.0	43.1	54.2	25	90066
70.0	67.0	79.8	10	920179