

HSSV-ZE



TECHNICAL DATA

Combined quick- insert corrugated tubes cable gland

Temperature range -25°C to +100°C
Protection class IP 65

STRUCTURE

- Material: Polyamide (PA) 6

PROPERTIES

- halogen-free
- cadmium-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- Combined quick-insert cable glands for a reliable, quick connection with strain relief.
Suitable for parallel-coiled HELUcond protection tubes.

NOTES

- Threaded connection:
metric to EN 60423
Each unit includes 1 safety opener

metric thread

Size	Suitable for nominal size	Thread length mm	Packaging unit (in pc.)	grey	black
				Part no.	Part no.
M16 x 1.50	10.0	7.5	50	903459	903466
M16 x 1.50	12.0	7.5	50	903460	903467
M20 x 1.50	17.0	8.5	50	903461	903468
M25 x 1.50	23.0	10.5	50	903462	903469
M32 x 1.50	29.0	10.5	25	903463	903470