



TECHNICAL DATA

PVDF sealing billets

Temperature range -30°C to +100°C

■ STRUCTURE

- Material:
 - black (RAL 9005): polyvinylidene fluoride (PVDF)
 - natural: Polyamide (PA)
 - white: Polyoxymethylen (POM)

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- For not assigned penetrations.

■ NOTES

- Legend:
 - Dimensions
 - L - Length
 - d - Inner diameter

Packaging unit (in pc.)	Diameter x Length mm	natural	black (RAL 9005)	white
		Part no.	Part no.	Part no.
100	3.0 x 25.00	11022886	903515	-
100	4.0	-	903516	-
100	4.0 x 25.00	11022563	903517	-
100	5.0 x 25.00	11022564	-	-
100	5.3 x 25.00	-	903518	-
100	6.0 x 25.00	-	903519	-
100	6.0 x 28.00	11022565	-	-
100	6.4 x 25.00	-	903520	903507
100	7.0 x 25.00	-	903521	-
100	7.0 x 28.00	11022566	-	-
100	7.5 x 20.00	-	903522	-
100	8.0 x 20.00	-	903523	-
100	8.0 x 30.00	11022567	-	-
100	9.0 x 20.00	-	903524	-
100	9.3 x 20.00	-	903525	-
100	10.0 x 20.00	-	903526	-
100	10.0 x 30.00	11022888	-	-
100	12.0 x 30.00	11023246	-	-