

JUMBO-FP



TECHNICAL DATA

One-piece straight flange connection

Temperature range -40°C to +120°C
Protection class IP 54 / IP 69K

■ STRUCTURE

- Material: Polyamide (PA) 6
- Flammability acc. to UL 94 (V0)

■ PROPERTIES

- halogen-free

- silicone-free
- cadmium-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- Suitable for parallel-coiled JUMBO protection tubes.

Suitable for nominal size	Weight kg, approx.	Packaging unit (in pc.)	grey	black
			Part no.	Part no.
70.0	10.80	1	90402	920368
95.0	16.90	1	90403	920369