

# JUMBO PA6



## TECHNICAL DATA

### PA Corrugated tubes

Temperature range	-40°C to +140°C short term up to +160°C
Capacity/100mm	approx. 1200, 800 N

## STRUCTURE

- Material: modified Polyamide (PA) 6
- Flammability acc. to UL 94 (V0)

## PROPERTIES

- halogen-free
- cadmium-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

## APPLICATION

- Machine and plant construction
  - Robotics
  - Automation technology
  - Vehicle construction and shipbuilding
  - Railway technology
  - Installation technology
  - Control cabinet construction
  - Oversize corrugated tubes
- Cable protection tube for medium to heavy-duty applications.

## NOTES

- Suitable connection glands:  
JUMBO gland
- Bending behaviour: very good

Suitable for nominal size	Inner Ø mm	Outer Ø mm, approx.	Bending radius mm	Packaging unit (in m)	grey	black
					Part no.	Part no.
70.0	66.5	79.2	200.0	10	<b>90408</b>	<b>91362</b>
95.0	91.0	106.0	265.0	10	<b>90409</b>	<b>91363</b>