

UNI-DICHT-VK-SS



TECHNICAL DATA

Stainless steel gland body

Temperature range up to +200°C

■ STRUCTURE

- Material: Stainless steel 1.4305 / AISI 303

■ PROPERTIES

- large temperature range
- high corrosion resistance

■ TESTS

- Test standard EN 62444

■ APPLICATION

- chemical industry
- Food and beverage industry
- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction
- For populating with inserts made of TPE or silicone. For use in chemical industry, at high temperatures, or long lasting UV-stress.

■ NOTES

- Legend:
Dimensions
TD - Thread Diameter
TL - Thread Length
SZ - Spanner Size

metric thread

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904247	M12 x 1.5	5.0	14	50
904248	M16 x 1.5	6.0	19	50
904249	M20 x 1.5	6.5	22	50
904250	M25 x 1.5	7.5	27	50

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904251	M32 x 1.5	8.0	36	25
904252	M40 x 1.5	8.0	46	10
904253	M50 x 1.5	10.0	55	5