



## TECHNICAL DATA

### Protection tube

Temperature range	-40°C to +100°C short term up to +120°C
Protection class	IP 68

- silicone-free
- cadmium-free
- resistant to: oil, petrol, microbes, weather-resistant
- largely resistant to: acids, alkalis
- extremely flexible, expandable and compressible

## ■ STRUCTURE

- Material: Polyurethane (PUR)
- Outer sheath material: Polyurethane (PUR)
- integrated spring steel wire

## ■ APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction

## ■ PROPERTIES

- halogen-free

## ■ NOTES

- Suitable connection glands: USK, LKI, US and LI

### blue - small pack

Part no.	Inner Ø mm	Outer Ø mm, approx.	Weight kg, approx.	Packaging unit (in m)
94870	7.0	10.0		10
94871	10.0	14.0		10
94872	13.0	17.0		10
94873	15.0	19.0		10
94874	16.0	21.0		10
94875	22.0	27.0		10
94876	29.0	36.0		10
94877	38.0	45.0		10
94879	48.0	56.0		10

### blue

Part no.	Inner Ø mm	Outer Ø mm, approx.	Weight kg, approx.	Packaging unit (in m)
90464	7.0	10.0	0.038	50
90465	10.0	14.0	0.085	50
90466	13.0	17.0	0.116	50
90467	15.0	19.0	0.119	50
90468	16.0	21.0	0.16	50
90469	22.0	27.0	0.26	50
90470	29.0	36.0	0.42	25
90471	38.0	45.0	0.50	25
90473	48.0	56.0	0.82	25