

HELUquick straight



TECHNICAL DATA

Corrugated tubes conduit gland

Temperature range	-40°C to +120°C
Protection class	IP 68 / IP 68

■ STRUCTURE

- Material: Polyamide (PA) 6

■ PROPERTIES

- halogen-free

- silicone-free
- cadmium-free
- resistant to: oil, petrol, weak acids, weak bases

■ APPLICATION

- Quick-insert glands with metallic female thread for a reliable, quick connection. Suitable for parallel-coiled HELUcond protection tubes

■ NOTES

- UR-tested
Disassembly without additional opener. Also available angled (45° and 90°).

metric thread

Size	Suitable for nominal size	Thread length mm	Spanner size mm	Packaging unit (in pc.)	grey	black
					Part no.	Part no.
M12 x 1.50	7.5	11.5	16	50	904797	904820
M12 x 1.50	10.0	12.0	18	50	904798	904821
M16 x 1.50	10.0	11.5	18	50	904799	904822
M16 x 1.50	12.0	11.5	21	50	904800	904823
M20 x 1.50	12.0	13.0	21	50	904801	904824
M20 x 1.50	17.0	13.0	27	50	904802	904825
M25 x 1.50	17.0	13.0	27	50	904803	904826
M25 x 1.50	23.0	13.0	34	25	904804	904827
M32 x 1.50	23.0	15.0	34	25	904861	904828
M32 x 1.50	29.0	15.0	40	25	904862	904829
M40 x 1.50	29.0	15.0	40	25	904863	904830
M40 x 1.50	37.0	17.0	55	25	904864	904831
M50 x 1.50	37.0	17.0	60	25	904865	904832
M50 x 1.50	50.0	17.0	65	10	904866	904833
M63 x 1.50	50.0	17.0	70	10	904867	904834