

PV-MC4



TECHNICAL DATA

PV-male and female cable coupler

Temperature range	-40°C to +90°C
Protection class	IP 67
Safety class	II
Rated voltage	1000 V (IEC)

Rated current	22A (2.5 mm ²), 30A (4mm ² , 6mm ²)
Contact resistance	0.35 mOhm

■ STRUCTURE

- Material: Polyamide (PA)
- Contact: Cu, tinned, rotated
- with Snap-in lock

MC4 male cable coupler

cross-section from / to mm ²	Cable Ø from / to mm	10	100	1000
		Part no. Packaging unit (in pc.)	Part no. Packaging unit (in pc.)	Part no. Packaging unit (in pc.)
2.50	3.0 - 6.0	11024796	11024814	905206
2.50	5.5 - 9.0	11024798	11024816	905208
4.00 - 6.00	3.0 - 6.0	11024800	11024818	905210
4.00 - 6.00	5.5 - 9.0	11024623	11024820	904963
10.00	5.5 - 9.0	-	-	905863

MC4 female cable coupler

cross-section from / to mm ²	Cable Ø from / to mm	10	100	1000
		Part no. Packaging unit (in pc.)	Part no. Packaging unit (in pc.)	Part no. Packaging unit (in pc.)
2.50	3.0 - 6.0	11024797	11024815	905207
2.50	5.5 - 9.0	11024799	11024817	905209
4.00 - 6.00	3.0 - 6.0	11024801	11024819	905211
4.00 - 6.00	5.5 - 9.0	11024624	11024821	904964
10.00	5.5 - 9.0	-	-	905864