

# SK-D



## TECHNICAL DATA

Polyolefin shrink tube 3:1

Temperature range -55°C to +110°C

### ■ STRUCTURE

- Material: Polyolefin
- with interior adhesive

### ■ PROPERTIES

- halogen-free
- thick walled
- very good chemical resistance

### ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction
- for repairing insulation
- for sealing electrical components
- for the protection of cable sleeves and terminations for low-voltage applications (600V)
- good protection against impact and abrasion

### ■ NOTES

- Approval: UR-listed up to size 68.1 mm

## rods

Inner Ø before shrinkage mm	Wall thickness mm	Inner Ø after shrinkage mm	Packaging unit (in m)	black Part no.
8.9	1.8	3	1.22	<b>905344</b>
13	2.4	4.1	1.22	<b>905335</b>
19.1	2.4	6.1	1.22	<b>905336</b>
27.9	3.0	8.9	1.22	<b>905337</b>
38.1	4.1	11.9	1.22	<b>905338</b>
50.8	4.1	16	1.22	<b>905339</b>
68.1	4.1	22.1	1.22	<b>905340</b>
89.9	4.1	30	1.22	<b>905731</b>
119.9	4.3	39.9	1.22	<b>905732</b>