

# HTP-CR



### TECHNICAL DATA

Clamping ring

Temperature range -45°C to +105°C

### ■ STRUCTURE

- Material: Brass nickel plated

### ■ APPLICATION

- Clamping rings for braided sleeve HTP.  
To assemble the tube connectors LT to the high temperature protection tube HTP.  
The plastic clamp ring is replaced by the brass clamp ring.

### ■ NOTES

- In conjunction with the tube connectors LT: Protection classification IP 54

Part no.	Size	trade size mm	Packaging unit (in pc.)
905439	M16 x 1.5	13.0	10
905555	M20 x 1.5	16.0	10
905440	M25 x 1.5	22.0	5
905557	M32 x 1.5	25.0	5

Part no.	Size	trade size mm	Packaging unit (in pc.)
905558	M40 x 1.5	35.0	2
905559	M50 x 1.5	38.0	2
905441	M63 x 1.5	51.0	2