

# SD-XXL

## gas and watertight gland



### TECHNICAL DATA

#### Nickel plated brass cable gland

Temperature range	-20°C to +100°C
Protection class	IP 68 - 5 bar

### ■ STRUCTURE

- Material: Brass, nickel plated
- Seal: Nitrile butadiene rubber (NBR)
- O-ring: Nitrile butadiene rubber (NBR)

### ■ PROPERTIES

- easy to assemble, time and cost savings
- Large-area sealing

- large clamping areas

### ■ TESTS

- Test standard EN 62444

### ■ APPLICATION

- For very large cable diameters. The quality is similar to an incision sealing ring and guarantees extensive clamping ranges.

### ■ NOTES

- Legend:  
Dimensions  
TD - Thread Diameter  
TL - Thread Length  
SZ - Spanner Size

### metric thread

Part no.	Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
905570	M72 x 2.0	56.0 - 62.0	16.0	77	4
905506	M75 x 1.5	56.0 - 62.0	16.0	77	4
905571	M75 x 2.0	56.0 - 64.0	16.0	90	4
905573	M80 x 2.0	50.0 - 56.0	18.0	90	2
905572	M80 x 2.0	60.0 - 67.0	18.0	90	2
905575	M85 x 2.0	63.0 - 70.0	22.0	95	2
905574	M85 x 2.0	68.0 - 77.0	22.0	95	2
905576	M90 x 2.0	68.0 - 77.0	22.0	100 / 95	2
905577	M110 x 2.0	60.0 - 82.0	25.0	125 / 120	2