


HELUTOP® HT-MFDE



TECHNICAL DATA

NBR multiple sealing insert

Temperature range -20°C to +100°C

■ STRUCTURE

- Material: Nitrile butadiene rubber (NBR)

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- For populating the HELUTOP® HT gland bodies made by polyamide or by brass.

■ NOTES

- Inserts for size M16x1,5 are suitable for cable glands M16x1,5 with clamping range 5-10mm.
- Legend:
 - D - Outer diameter
 - d - Inner diameter
 - H - Height

Part no.	Size	Sealing insert colour	Number holes x cable-Ø mm	Packaging unit (in pc.)
905773	M16 x 1.5	black	2 x 2.0	1000
905774	M16 x 1.5	black	2 x 3.0	250
920102	M16 x 1.5	black	2 x 4.0	200
905776	M16 x 1.5	black	3 x 4.0	250
905775	M16 x 1.5	black	2 x 5.0	50
920109	M20 x 1.5	black	4 x 3.0	50
920105	M20 x 1.5	black	3 x 4.0	50
905777	M20 x 1.5	black	4 x 4.0	50
920103	M20 x 1.5	black	2 x 5.0	50
920106	M20 x 1.5	black	3 x 5.0	50
920104	M20 x 1.5	black	2 x 6.0	50
903529	M25 x 1.5	black	7 x 3.0	50
905779	M25 x 1.5	black	5 x 4.0	250
920117	M25 x 1.5	black	6 x 4.0	50
905778	M25 x 1.5	black	3 x 5.0	250
920114	M25 x 1.5	black	4 x 5.0	50
920110	M25 x 1.5	black	2 x 6.0	50
920112	M25 x 1.5	black	3 x 6.0	50
920113	M25 x 1.5	black	3 x 7.0	50
903531	M32 x 1.5	black	9 x 3.0	50

Part no.	Size	Sealing insert colour	Number holes x cable-Ø mm	Packaging unit (in pc.)
905783	M32 x 1.5	black	8 x 4.0	50
920129	M32 x 1.5	black	9 x 4.0	50
920126	M32 x 1.5	black	6 x 5.0	50
905784	M32 x 1.5	black	8 x 5.0	50
920123	M32 x 1.5	black	4 x 6.0	50
920125	M32 x 1.5	black	5 x 6.0	50
903530	M32 x 1.5	black	6 x 6.0	50
905780	M32 x 1.5	black	2 x 7.0	50
905782	M32 x 1.5	black	4 x 7.0	50
920119	M32 x 1.5	black	2 x 8.0	50
920122	M32 x 1.5	black	3 x 8.0	50
904926	M32 x 1.5	black	4 x 8.0	50
920120	M32 x 1.5	black	2 x 9.0	50
905790	M40 x 1.5	black	8 x 6.0	50
905789	M40 x 1.5	black	6 x 7.0	50
905791	M40 x 1.5	black	9 x 7.0	50
905787	M40 x 1.5	black	4 x 8.0	50
905785	M40 x 1.5	black	2 x 10.0	50
905786	M40 x 1.5	black	3 x 10.0	50