



## TECHNICAL DATA

### Spiral wound stainless steel tube

Temperature range	-100°C to +600°C
Protection class	IP 40

## ■ STRUCTURE

- Material: Stainless steel
- with double-folded profile (Agraff profile)

## ■ PROPERTIES

- high tensile and torsional strength

## ■ APPLICATION

- Robotics
- Steel and aluminium foundry industry
- Maschine and apparatus building
- Off-shore-industry
- Security
- Metal, glass and ceramics industry

## ■ NOTES

- Suitable connection glands: LT-E-UI

Part no.	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)
905804	9.5	12.5	30
905805	13.0	16.0	30
905806	17.0	21.0	30
905807	22.0	26.0	30

Part no.	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)
905808	26.0	30.0	30
905809	34.0	39.0	30
905810	40.3	44.4	15
905811	51.6	55.7	15