

LT-E-UI elbow 90°



TECHNICAL DATA

Stainless steel- conduit gland

Temperature range -55°C to +260°C
Protection class IP 40

■ STRUCTURE

- Material: Stainless steel
- Seal: Nitrile butadiene rubber (NBR)
- Grounding sleeve: Brass nickel plated
- Sealing ring: Brass nickel plated

■ PROPERTIES

- halogen-free

■ APPLICATION

- Robotics
- Steel and aluminium foundry industry
- Maschine and apparatus building
- Off-shore-industry
- Security
- Metal, glass and ceramics industry
- LIQUIDTIGHT conduit gland for stainless steel protection tubes UI. The conical earthing sleeve offers maximum surface contact for optimum sealing and earthing.

metric thread

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Inner Ø mm	Packaging unit (in pc.)
905832	M16 x 1.5	12.5	12.0	6.8	10
905833	M16 x 1.5	16.0	12.0	9.8	10
905834	M20 x 1.5	12.5	13.0	6.8	10
905835	M20 x 1.5	16.0	13.0	9.8	10
905836	M20 x 1.5	21.0	13.0	13.9	10
905837	M25 x 1.5	26.0	15.0	18.5	5

PG thread

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Inner Ø mm	Packaging unit (in pc.)
905838	PG 11	12.5	12.0	6.8	10
905839	PG 11	16.0	12.0	9.8	10
905840	PG 16	21.0	13.0	13.9	10
905841	PG 21	26.0	15.0	18.5	5
905842	PG 29	30.0	15.0	22.8	5

LT-E-UI elbow 90°

NPT thread

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Inner Ø mm	Packaging unit (in pc.)
905847	NPT 1"	30.0	15.0	22.8	5
905843	NPT 1/2"	12.5	12.0	6.8	10
905844	NPT 1/2"	16.0	12.0	9.8	10
905845	NPT 1/2"	21.0	13.0	13.9	10
905846	NPT 3/4"	26.0	15.0	18.5	5