

# T-SK/SKU



## TECHNICAL DATA

Steel lug lock cable tie

Temperature range -40°C to +85°C

## STRUCTURE

- Material: Polyamide (PA) 6.6
- Flammability acc. to UL 94 (V2)

## PROPERTIES

- halogen-free
- silicone-free
- self-extinguishing
- high requirements to flexibility and resistance, also at low temperatures and dry climate
- high tension due to extra wide steel lugs
- corrosion resistant and non-magnetic V4A stainless steel

## APPLICATION

- for directionality and mounting

## T-SK

Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	transparent Part no.
T-SK 2-24	100.0	2.5	24	135	1000	<b>907016</b>
T-SK 2-55	200.0	2.5	55	135	1000	<b>907017</b>
T-SK 3-36	140.0	3.5	36	200	1000	<b>907018</b>
T-SK 3-55	200.0	3.5	55	200	1000	<b>907019</b>
T-SK 3-80	280.0	3.5	80	200	1000	<b>907020</b>
T-SK 4-101	360.0	4.5	103	350	1000	<b>907023</b>
T-SK 4-51	186.0	4.5	49	350	1000	<b>907021</b>
T-SK 4-76	290.0	4.5	80	350	1000	<b>907022</b>
T-SK 7-95	340.0	7.0	90	600	500	<b>907037</b>

## T-SKU

Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	black Part no.
T-SKU 2-24	100.0	2.5	24	135	1000	<b>907024</b>
T-SKU 2-55	200.0	2.5	55	135	1000	<b>907025</b>
T-SKU 3-36	140.0	3.5	36	200	1000	<b>907026</b>
T-SKU 3-55	200.0	3.5	55	200	1000	<b>907027</b>
T-SKU 3-80	280.0	3.5	80	200	1000	<b>907028</b>
T-SKU 4-101	360.0	4.5	103	350	1000	<b>907031</b>
T-SKU 4-51	186.0	4.5	49	350	1000	<b>907029</b>

Continued on next page

# T-SK/SKU



Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	black Part no.
T-SKU 4-76	290.0	4.5	80	350	1000	<b>907030</b>
T-SKU 7-95	340.0	7.0	90	600	500	<b>907038</b>