

# KVA-VK-MS

with Soft PVC



## TECHNICAL DATA

Nickel plated brass gland body

Temperature range -30°C to +100°C

### ■ STRUCTURE

- Material: Brass, nickel plated
- O-ring: Nitrile butadiene rubber (NBR)

### ■ TESTS

- Test standard EN 62444

### ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- For fitting with inserts.

### ■ NOTES

- Legend:  
Dimensions  
TD - Thread Diameter  
TL - Thread Length  
SZ - Spanner Size

#### metric thread

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)
90788	M12 x 1.5	6.0	14	100
90789	M16 x 1.5	6.5	17	100
90790	M20 x 1.5	7.0	22	50
90792	M25 x 1.5	7.5	27	50

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)
91367	M32 x 1.5	8.0	35	25
90794	M40 x 1.5	8.0	43	10
90795	M50 x 1.5	10.0	54	10
90796	M63 x 1.5	10.0	65	5

#### PG thread

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)
96033	PG 7	5.0	14	100
96034	PG 9	6.0	17	100
96035	PG 11	6.0	20	50
96036	PG 13.5	6.5	22	50
96037	PG 16	6.5	24	50

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)
96038	PG 21	7.0	30	25
96039	PG 29	8.0	40	10
96040	PG 36	9.0	50	10
96041	PG 42	10.0	57	5
96042	PG 48	10.0	64	10