

Anaconda Sealtite® NMFG-Clean



TECHNICAL DATA

PVC corrugated tube

Temperature range	-35°C to +60°C short term up to +80°C
Protection class	IP 67

■ STRUCTURE

- Material: Special Polyvinylchlorid (PVC) according to FDA CFR 21 and NSF 51 (USA standard)
- with integrated Hard PVC spiral

■ PROPERTIES

- resistant to: chemical cleaning supplies
- thick, soft, smooth and thermoplastic PVC tube

- liquid tight
- prevents to adhere harmful microorganisms
- easy and fast cleaning because of the smooth surface
- high flexible

■ APPLICATION

- Food and beverage industry
- Pharmaindustrie
- Biotechnologie
- chemical industry

■ NOTES

- Suitable connection glands: LT-FG-Clean (up to M50), LT-straight, LT-angled, LT-E-UI-straight, LT-E-UI-angled

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Bending radius mm	Bending radius dyna- mic mm	Packaging unit (in pc.)	blue Part no.
3/8	12.6	17.8	70.0	100.0	30	908211
1/2	16.0	21.1	100.0	135.0	30	908212
3/4	21.1	26.4	130.0	175.0	30	908213
1	26.8	33.1	180.0	220.0	30	908214
1 1/4	35.4	41.8	225.0	270.0	15	908215
1 1/2	40.3	47.8	255.0	320.0	15	908216
2	51.6	59.9	310.0	400.0	15	908217