

# Anaconda Sealtite® NMFG-Clean



## TECHNICAL DATA

PVC corrugated tube

**Temperature range** -35°C to +60°C  
short term up to +80°C

**Protection class** IP 67

## ■ STRUCTURE

- Material: Special polyvinyl chloride (PVC) according to FDA CFR 21 and NSF 51 (USA standard)
- with integrated Hard PVC spiral

## ■ PROPERTIES

- resistant to: chemical cleaning supplies
- thick, soft, smooth and thermoplastic PVC tube

- liquid tight
- prevents to adhere harmful microorganisms
- easy and fast cleaning because of the smooth surface
- high flexible

## ■ APPLICATION

- Food and beverage industry
- Pharmaindustrie
- Biotechnologie
- chemical industry

## ■ NOTES

- Suitable connection glands:  
LT-FG-Clean (bis M50)  
LT-straight  
LT-elbow 45° und 90°  
LT-E-UI- elbow 90°

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Bending radius mm	Bending radius dyna- mic mm	Packaging unit (in pc.)	blue Part no.
3/8	12.6	17.8	70.0	100.0	30	<b>908211</b>
1/2	16.0	21.1	100.0	135.0	30	<b>908212</b>
3/4	21.1	26.4	130.0	175.0	30	<b>908213</b>
1	26.8	33.1	180.0	220.0	30	<b>908214</b>
1 1/4	35.4	41.8	225.0	270.0	15	<b>908215</b>
1 1/2	40.3	47.8	255.0	320.0	15	<b>908216</b>
2	51.6	59.9	310.0	400.0	15	<b>908217</b>