

# HELUTOOL HHPI 20



TECHNICAL DATA

Hydraulic hand press in toolbox

■ APPLICATION

- extremely fast operation through two-stage hydraulic pump
- large processing area up to 300mm<sup>2</sup>
- rotatable quick release head 180 °
- with folding clasp for effortless operation even in hard reach places
- lightweight and portable, compact design
- built-in pressure relief valve, even in the case of a false pressing no damage to the tool and inserts
- universally applicable: inserts are available for all cable lug types
- Press capacity: ca. 62 kN

■ NOTES

- Exclusive inserts  
Matching inserts:  
HELU-S-PE-SK and HELU-S-PE-WM  
Further inserts on request  
Including plastic toolbox

Part no.	Type	Length mm	Weight kg, approx.	Packaging unit (in pc.)
908286	HHPI 20	396.0	2.80	1