

CTSS-E



TECHNICAL DATA

Stainless steel cable ties

Temperature range -80°C to +538°C

■ STRUCTURE

- Material: Stainless steel 1.4401 / AISI 316
- with ball lock

■ PROPERTIES

- resistant to: aggressive chemicals
- corrosion resistant
- radiation resistant
- anti-magnetic
- temperature-resistant

■ APPLICATION

- For use in extreme conditions, such as high temperatures, aggressive environment, high tensile load.

Part no.	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)
90900	150.0	4.6	35	778	100
90901	200.0	4.6	50	778	100
90902	290.0	4.6	75	778	100
90903	360.0	4.6	100	778	100

Part no.	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)
90904	200.0	7.9	50	1559	100
90905	290.0	7.9	75	1559	100
90906	360.0	7.9	100	1559	100
90907	520.0	7.9	150	1559	25