



## TECHNICAL DATA

Steel lug lock cable tie

Temperature range -60°C to +85°C

## STRUCTURE

- Material: Polyamide (PA) 6.6
- Flammability acc. to UL 94 (V2)

## PROPERTIES

- halogen-free
- silicone-free

## APPLICATION

- Cable tie with steel lug lock made of corrosion-resistant, non-magnetic steel. This technology enables the cable tie to offer excellent binding properties even under the most rigorous conditions such as heat, cold, humidity etc. and makes it insensitive to vibrations and external influences.

## NOTES

- Brown, red, orange, yellow, green, purple or grey available on request.

Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	transparent Part no.
TYB 23M	92.0	2.4	16	80	1000	<b>91051</b>
TY 232M	203.0	2.4	50	80	1000	<b>91055</b>
TY 234M	356.0	2.4	102	80	1000	<b>91058</b>
TYB 24M	140.0	3.6	29	180	1000	<b>91061</b>
TY 242M	204.0	3.6	50	180	1000	<b>91064</b>
TY 26M	284.0	3.6	76	130	1000	<b>91067</b>
TY 244M	368.0	3.6	103	130	1000	<b>91070</b>
TYB 25M	186.0	4.8	45	220	1000	<b>91073</b>
TY 253M	295.0	4.8	78	220	1000	<b>91076</b>
TY 28M	361.0	4.8	102	220	1000	<b>91079</b>
TY 272M	223.0	6.9	50	540	500	<b>91082</b>
TY 27M	340.0	6.9	90	540	500	<b>91085</b>
TY 29M	771.0	6.9	229	540	500	<b>91088</b>

## small pack

Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	transparent Part no.
TY 5-23M	92.0	2.4	16	80	100	<b>91050</b>
TY 5-232M	203.0	2.4	50	80	100	<b>91054</b>

# TY-RAP®-T



Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	transparent Part no.
TY 5-234M	356.0	2.4	102	80	100	<b>91057</b>
TY 5-24M	140.0	3.6	29	180	100	<b>91060</b>
TY 5-242M	204.0	3.6	50	180	100	<b>91063</b>
TY 5-26M	284.0	3.6	76	130	100	<b>91066</b>
TY 5-244M	368.0	3.6	103	130	100	<b>91069</b>
TY 5-25M	186.0	4.8	45	220	100	<b>91072</b>
TY 5-253M	295.0	4.8	78	220	100	<b>91075</b>
TY 5-28M	361.0	4.8	102	220	100	<b>91078</b>
TY 5-272M	223.0	6.9	50	540	50	<b>91081</b>
TY 5-27M	340.0	6.9	90	540	50	<b>91084</b>
TY 5-29M	771.0	6.9	229	540	50	<b>91087</b>