



TECHNICAL DATA

Steel lug lock cable tie

Temperature range -60°C to +105°C

■ STRUCTURE

- Material: Polyamide (PA) 6.6
- Flammability acc. to UL 94 (V2)

■ PROPERTIES

- halogen-free

- silicone-free

■ APPLICATION

- UV-stabilised cable tie with steel lug lock made of corrosion-resistant, non-magnetic steel. This technology enables the cable tie to offer excellent binding properties even under the most rigorous conditions such as heat, cold, humidity etc. and makes it insensitive to vibrations and external influences.

■ NOTES

- Other colours and materials available on request.

Part no.	Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)
91052	TYB 23MX	92.0	2.4	16	80	1000
91056	TY 232MX	203.0	2.4	50	80	1000
91059	TY 234MX	356.0	2.4	102	80	1000
91062	TYB 24MX	140.0	3.6	29	180	1000
91065	TY 242MX	204.0	3.6	50	180	1000
91068	TY 26MX	284.0	3.6	76	130	1000
91071	TY 244MX	368.0	3.6	103	130	1000

Part no.	Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)
91074	TYB 25MX	186.0	4.8	45	220	1000
91077	TY 253MX	295.0	4.8	78	220	1000
91080	TY 28MX	361.0	4.8	102	220	1000
91083	TY 272MX	223.0	6.9	50	540	500
91086	TY 27MX	340.0	6.9	90	540	500
91089	TY 29MX	771.0	6.9	229	540	500

small pack

Part no.	Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)
97310	TY 5-23MX	92.0	2.4	16	80	100
97311	TY 5-232MX	203.0	2.4	50	80	100
97312	TY 5-234MX	356.0	2.4	102	80	100
97313	TYB 5-24MX	140.0	3.6	29	180	100
97314	TY 5-242MX	204.0	3.6	50	180	100
97436	TY 5-26MX	284.0	3.6	76	130	100
97437	TY 5-244MX	368.0	3.6	103	130	100

Part no.	Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)
93694	TY 5-25MX	186.0	4.8	45	220	100
93695	TY 5-253MX	295.0	4.8	78	220	100
93696	TY 5-28MX	361.0	4.8	102	220	100
93697	TY 5-272MX	223.0	6.9	50	540	50
93698	TY 5-27MX	340.0	6.9	90	540	50
93699	TY 5-29MX	771.0	6.9	229	540	50