



TECHNICAL DATA

Steel lug lock cable tie

Temperature range -60°C to +85°C

■ STRUCTURE

- Material: Polyamide (PA) 6.6
- with steel lug lock made of corrosion-resistant, non-magnetic steel
- Flammability acc. to UL 94 (V2)

■ PROPERTIES

- halogen-free
- silicone-free

■ APPLICATION

- This technology enables the cable tie to offer excellent binding properties even under the most rigorous conditions such as heat, cold, humidity etc. and makes it insensitive to vibrations and external influences.

with assembly hole

Part no.	Type	Colour	Length mm	Width mm	Bundle Ø mm	Capacity N	Hole Ø mm	Packaging unit (in pc.)
91093	TY 33M	transparent	102.0	2.3	16	80	3	1000
91094	TY 34M	transparent	151.0	3.5	29	180	4.4	1000
91095	TY 635M	transparent	198.0	4.7	45	220	4	1000
91096	TY 35M	transparent	199.0	4.7	45	220	5.1	1000
91098	TY 37M	transparent	256.0	7.7	90	540	6.7	500

with plug-in clip

Part no.	Type	Colour	Length mm	Width mm	Bundle Ø mm	Capacity N	Hole Ø mm	Packaging unit (in pc.)
91103	TY 38M	transparent	200.0	4.7	44	220		1000