

USH



TECHNICAL DATA

Corrugated protection tube holder

Temperature range -30°C to +100°C

■ STRUCTURE

- Material: Polycarbonat (PC)
- with flange pipe holder
- Flammability acc. to UL 94

■ PROPERTIES

- halogen-free
- phosphor-free
- cadmium-free
- resistant to: alkalis, weak acids, fuels, alcohol, mineral oils

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- Tube holder for HELUcond protection tube. Universal, high-strength tube holder with double struts. Fastening bores suitable for horizontal and vertical rail systems in control cabinet.

Suitable for tube outer Ø mm	Width mm	Height mm	Packaging unit (in pc.)	grey	black
				Part no.	Part no.
21.0	38.0	40	50	91200	93497
28.5	38.0	40	50	91201	93498
34.5	38.2	48	50	91202	93499
42.5	60.4	59	50	91203	93507
54.5	59.7	77	50	91204	93508