

# PT-S



## TECHNICAL DATA

### Protection tube

Temperature range	-25°C to +90°C short term up to +100°C
Protection class	IP 68

## ■ STRUCTURE

- Material: Polyvinyl chloride (PVC)

## ■ PROPERTIES

- silicone-free

- cadmium-free
- largely resistant to: oil, acids
- extremely flexible, expandable and compressible

## ■ APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction
- Cable protection tube type S with integrated spring steel wire.

## ■ NOTES

- Suitable connection glands: USK, LK-I, MTG-US und MTG-LI

Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey Part no.
7.0	10.0	50	91219
10.0	14.0	50	91220
13.0	17.0	50	91221
15.0	19.0	50	91222
16.0	21.0	50	91223
22.0	27.0	50	91224
29.0	36.0	25	91225
38.0	45.0	25	91226
44.0	52.0	25	91227
48.0	56.0	25	91228

### small pack

Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey Part no.
7.0	10.0	10	91270
10.0	14.0	10	91271
13.0	17.0	10	91272
15.0	19.0	10	91273
16.0	21.0	10	91274
22.0	27.0	10	91275
29.0	36.0	10	91276

Continued on next page

# PT-S

Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey Part no.
38.0	45.0	10	<b>91277</b>
48.0	56.0	10	<b>91279</b>