

# Anaconda Sealtite® EF



## TECHNICAL DATA

### Protection tube

Temperature range	-25°C to +70°C short term up to +90°C
Protection class	IP 67

- continuous cord seal
- extruded plastic sheath

## APPLICATION

- Universal applications.  
Due to the complex construction method, the plastic sheath and internal tube flush together.

## STRUCTURE

- Material: steel galvanized
- Outer sheath material: Polyvinylchlorid (PVC)
- reinforced, galvanised and spiral wound steel band
- with latched profile

## NOTES

- Suitable connection glands:  
LT-straight, LT-elbow 45° and 90°  
CV Compact straight, CV Compact elbow 45° and 90°

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey	black
				Part no.	Part no.
1/4	6.4	11.5	50	<b>91229</b>	<b>96939</b>
5/16	10.1	14.4	50	<b>91230</b>	<b>96248</b>
3/8	12.6	17.8	75	<b>91231</b>	<b>96249</b>
1/2	16.0	21.1	60	<b>91232</b>	<b>97153</b>
3/4	21.0	26.4	50	<b>91233</b>	<b>96718</b>
1	26.5	33.1	30	<b>91234</b>	<b>96250</b>
1 1/4	35.1	41.8	30	<b>91235</b>	<b>96251</b>
1 1/2	40.3	47.8	15	<b>91236</b>	<b>97175</b>
2	51.6	59.9	15	<b>91237</b>	<b>96252</b>

## small pack

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey	black
				Part no.	Part no.
5/16	10.1	14.4	10	<b>94915</b>	<b>94930</b>
3/8	12.6	17.8	10	<b>94916</b>	<b>94931</b>
1/2	16.0	21.1	10	<b>94917</b>	<b>94932</b>
3/4	21.0	26.4	10	<b>94918</b>	<b>94933</b>