

Anaconda Sealite® OR



TECHNICAL DATA

Protection tube

Temperature range -15°C to +100°C
short term up to +120°C

Protection class IP 67

STRUCTURE

- Material: steel galvanized
- Outer sheath material: Polyvinylchlorid (PVC)
- reinforced, galvanised and spiral wound steel band
- with latched profile
- continuous cord seal
- extruded plastic sheath

PROPERTIES

- resistant to: oil, greases, alkalis, acids
- UV resistant

APPLICATION

- Due to the complex construction method, the plastic sheath and internal tube flush together.

NOTES

- Suitable connection glands:
LT-straight, LT-elbow 45° and 90°
CV Compact straight, CV Compact elbow 45° and 90°

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	black Part no.
3/8	12.6	17.8	75	91245
1/2	16.0	21.1	60	91246
3/4	21.0	26.4	50	91247
1	26.5	33.1	30	91248
1 1/4	35.1	41.8	30	91249
1 1/2	40.3	47.8	15	91250
2	51.6	59.9	15	91251