

Anaconda Sealtite® CNP



TECHNICAL DATA

Plastic tube

Temperature range -20°C to +60°C
short term up to +80°C

Protection class IP 67

■ STRUCTURE

- Material: Polyvinyl chloride (PVC)
- Outer sheath material: Special polyvinyl chloride (PVC)
- with woven nylon insert

■ PROPERTIES

- resistant to: oil, greases

■ APPLICATION

- Fully plastic.
Extremely abrasion-resistant plastic tube for heavy-duty applications.

■ NOTES

- Suitable connection glands:
LT-CNP and LT-CNP-E

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	orange Part no.
3/8	12.6	19.4	76	91259
1/2	16.1	23.4	60	91260
3/4	21.0	29.5	53	91261
1	26.5	36.3	30	91262
1 1/4	35.1	46.0	15	91263
1 1/2	40.7	52.4	15	91264
2	52.4	66.6	15	91265