

HSB-Boxes



TECHNICAL DATA

Polyolefin shrink tube 2:1

Temperature range -55°C to +135°C

■ STRUCTURE

- Material: Polyolefin

■ PROPERTIES

- silicone-free

- cadmium-free
- lead-free

■ APPLICATION

- for repairing insulation
- for sealing electrical components

■ NOTES

- Form of shipment: HSB box
Other colours on request.
Halogen-free (transparent only)

Type	Inner Ø before shrinkage mm	Wall thickness mm	Inner Ø after shrinkage mm	Packaging unit (in pc.)	black	transparent
					Part no.	Part no.
HSB 46	1.2	0.4	0.6	1	91321	-
HSB 46-C	1.2	0.4	0.6	1	-	98519
HSB 63	1.6	0.4	0.8	1	91322	-
HSB 63-C	1.6	0.4	0.8	1	-	97085
HSB 93	2.4	0.5	1.2	1	91323	-
HSB 93-C	2.4	0.5	1.2	1	-	96277
HSB 125	3.2	0.5	1.6	1	91324	-
HSB 125-C	3.2	0.5	1.6	1	-	97485
HSB 187	4.7	0.5	2.4	1	91325	-
HSB 187-C	4.7	0.5	2.4	1	-	96687
HSB 250	6.4	0.6	3.2	1	91326	-
HSB 250-C	6.4	0.6	3.2	1	-	96830
HSB 375	9.5	0.6	4.7	1	91327	-
HSB 375-C	9.5	0.6	4.7	1	-	96761
HSB 500	12.7	0.7	6.4	1	91328	-
HSB 500-C	12.7	0.7	6.4	1	-	96752
HSB 750	19.1	0.7	9.5	1	91329	-
HSB 750-C	19.1	0.7	9.5	1	-	96751
HSB 1000	25.4	0.8	12.7	1	91330	-
HSB 1000-C	25.4	0.8	12.7	1	-	97107