

KVA-XXL-VK-MS



TECHNICAL DATA

Nickel plated brass gland body

Temperature range -20°C to +105°C

■ STRUCTURE

- Material: Brass, nickel plated
- Seal: Nitrile butadiene rubber (NBR)
- O-ring: Nitrile butadiene rubber (NBR)

■ TESTS

- Test standard EN 60423

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- For large cable diameters sealing inserts.

■ NOTES

- Legend:
Dimensions
TD - Thread Diameter
TL - Thread Length
SZ - Spanner Size

metric thread

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)
920144	M72 x 2.0	15.0	80	1
920145	M75 x 1.5	15.0	80	1

Part no.	Size	Thread length mm	Spanner size mm	Packaging unit (in pc.)
920146	M80 x 2.0	15.0	95	1