

HELUcond PA6-S



TECHNICAL DATA

PA Corrugated tubes

Temperature range	-40°C to +120°C short term up to +150°C
Capacity/100mm	approx. 350 N (NW: 17)

■ STRUCTURE

- Material: modified Polyamide (PA) 6
- Flammability acc. to UL 94 (V2)

■ PROPERTIES

- halogen-free
- cadmium-free

- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- Cable protection tube for medium to heavy-duty applications

■ NOTES

- Fine profile. Suitable connection glands: HELUquick, HSSV.

Nominal size mm	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey	black
				Part no.	Part no.
4.5	4.5	7.1	100	920154	920155
7.5	6.6	10.0	50	92724	92723
10.0	9.8	12.8	50	92676	92713
12.0	12.3	15.7	50	92677	92714
17.0	16.6	21.1	50	92678	92715
23.0	23.1	28.4	50	92679	92716
29.0	28.9	34.5	25	92685	92717
37.0	34.0	42.2	25	92686	92718
50.0	45.6	53.8	25	92687	92719