

HELUcond PP



TECHNICAL DATA

PP-corrugated tubes

Temperature range	-40°C to +130°C short term up to +150°C
Capacity/100mm	approx. 350 N (NW: 17)

■ STRUCTURE

- Material: Polypropylene (PP)
- Flammability acc. to UL 94 (HB)

■ PROPERTIES

- halogen-free
- cadmium-free

- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Machine and plant construction
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Chemical plants
- Heating and air-conditioning technology
- Cable protection tube for medium stress applications.

■ NOTES

- Fine profile.
Suitable connection glands: HELUquick, HSSV.

Nominal size mm	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	black Part no.
7.5	7.1	10.0	100	920170
10.0	9.9	13.0	50	920171
12.0	12.2	15.7	50	920172
14.0	14.2	18.2	50	920173
17.0	16.6	21.2	50	920174
23.0	23.2	28.3	50	920175
29.0	29.0	34.5	25	920176
37.0	36.0	42.4	25	920177
50.0	47.7	54.5	25	920178