

HSSV elbow 45° metal



TECHNICAL DATA

Corrugated tubes conduit gland

Temperature range	-40°C to +110°C
Protection class	IP 65

■ STRUCTURE

- Material: Polyamide (PA) 6
- Flammability acc. to UL 94 (V0)

■ PROPERTIES

- halogen-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- Quick-insert glands with metallic male thread for a reliable, quick connection.
Suitable for parallel-coiled HELUcond protection tubes.

■ NOTES

- UR-tested
Protection classification:
IP 66 with outer seal
Threaded connection: metric to EN 60423
Each unit includes 1 safety opener

metric thread

Size	Suitable for nominal size	Thread length mm	Packaging unit (in pc.)	grey	black
				Part no.	Part no.
M25 x 1.5	21 / 23	15.0	50	920265	920269
M32 x 1.5	29	15.0	25	920266	920270
M40 x 1.5	36 / 37	16.0	25	920267	920271
M50 x 1.5	48 / 50	16.0	10	920268	920272